



Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 250V, 6-20R, Ivory, Single Pack

By Bryant
Catalog # 5461I



Straight Blade Devices, Receptacles, Single,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A
250V, 6-20R, Ivory, Single Pack

Features

- Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 20A 250V
- 6-20R

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	5461I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786174184

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in

Length	3.28 in
Weight	0.1 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	6-20R
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	5500

Product Assets

[Catalog Page - BRY A-9 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 5461I](#)