



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Nylon Cup, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, White, Single Pack

By Bryant
Catalog # 5478



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Nylon Cup, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, White, Single Pack

Application

Extra Heavy Duty Industrial

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Single Flanged
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Clamp Type
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786662902

Dimensions

Dimensions	1.84 in x 2.50 in x 1.55 in
Display Size	Standard Sized Product
Height	1.55 in
Length	1.84 in
Weight	0.05 lb
Width	2.50 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	6-20P
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-5478-SPEC-EN | REV 5/2023