



## Straight Blade Devices, Receptacles, Panel Mount Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Brown, Single Pack

By Bryant  
Catalog # 5484



Straight Blade Devices, Receptacles, Panel Mount Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Brown, Single Pack

### Application

Extra Heavy Duty Industrial Specification Grade

### General

Color	Brown
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Panel Mount Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Specialty Receptacle
UPC	781786663008

### Dimensions

Dimensions	1.94 in x 1.38 in x 0.81 in
Display Size	Standard Sized Product
Height	0.81 in
Length	1.94 in
Weight	0.05 lb
Width	1.38 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

### Certifications and Compliance

Nema Rating	6-20R
-------------	-------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant Q-18 Catalog page](#)  
[Catalog Page - Bryant A-9 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-5484-SPEC-EN | REV 5/2023