



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 3-Phase Wye 277/480V AC, Watertight



By Bryant
Catalog # 560C7W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 60A 3-Phase Wye 277/480V AC, 4- Pole 5-Wire Grounding, Screw Terminals, Red, Watertight

Features

- Industrial Grade
- Female Connector Body
- 60A 3-Phase Wye 277/480V AC
- 4- Pole 5-Wire Grounding
- Screw Terminals

Application

High Ampacity Connections

General

Catalog Number	560C7W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector

UPC 781786251977

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Voltage Rating	3 Phase Y 277/480 V
Voltage Rating Description	3 Phase Y 277/480V

Conductor Related

Conductor Range	#8 AWG to #2 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding

Certifications And Compliance

Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Product Assets

[Specifications - 560C7W](#)