



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 63A 220-415V, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Watertight



By Bryant
Catalog # 563P6W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 63A 220-415V, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Watertight

General

Application	High Ampacity Connections
Catalog Number	563P6W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Type	Plugs
UPC	781786252097

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	63 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	63 A
Current Rating	63 A
Phase	Multi Phase
Voltage Rating	200/346 V 240/415 V
Voltage Rating Description	200/346 V 240/415 V
Wattage	26145

Conductor Related

Cord Type	All Portable
Number Of Wires	5-Wire
Wire Size	#8 AWG to #2 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets



A Hubbell brand