



Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 15A 250V, 6-15R, Red, Single Pack

By Bryant
Catalog # [5661RED](#)



Straight Blade Devices, Receptacles, Single,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
250V, 6-15R, Red, Single Pack

Application

Extra Heavy Duty Industrial Specification Grade

General

Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786625952

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in
Weight	0.15 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	6-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-9 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-5661RED-SPEC-EN | REV 6/2024