



# Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Self-Grounding Strap, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, Single Pack

By Bryant  
Catalog # 5678G



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, Self-Grounding Strap, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, White, Single Pack

## General

Application	Extra Heavy Duty Industrial
Catalog Number	5678G
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Single Flanged
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Clamp Type
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786626089

## Dimensions

Dimensions	1.84 in x 2.50 in x 1.55 in
Display Size	Standard Sized Product
Height	1.55 in
Length	1.84 in
Weight	0.1 lb
Width	2.5 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Nema Rating	6-15P
-------------	-------

## Logistics

Carton Quantity	100
-----------------	-----

## Product Assets

[Catalog Page - BRY A-10 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-5678G-SPEC-EN | REV 6/2024