



Straight Blade Devices, Receptacles, Panel Mount Single, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack

By Bryant
Catalog # [5684](#)



Straight Blade Devices, Receptacles, Panel Mount Single,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
250V, 6-15R, Brown, Single Pack

General

Color	Brown
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Specialty Receptacle
UPC	781786626072

Dimensions

Dimensions	1.94 in x 1.38 in x 0.81 in
Display Size	Standard Sized Product
Height	0.81 in
Length	1.94 in
Weight	0.05 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000 W

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	6-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant Q-18 Catalog page](#)
[Catalog Page - Bryant A-9 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-5684-SPEC-EN | REV 5/2023