



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 15A 277V AC, 7- 15R, Brown, Single Pack

By Bryant
Catalog # 5762



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
277V AC, 7- 15R, Brown, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 15A 277V AC
- 7- 15R

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	5762
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786664401

Dimensions

Dimensions	3.28 in x 1.38 in x 0.86 in
Display Size	Standard Sized Product
Height	0.86 in

Length	3.28 in
Weight	0.2 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	277 V
Voltage Rating Description	277 V
Wattage	4155

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	7-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-11 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 5762](#)