



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 277V AC, 7- 15R, Mounted to 4" Round Cover

By Bryant
Catalog # 5782



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 277V AC, 7- 15R, Brown, Single Pack, Mounted to 4" Round Cover

Application

Extra Heavy Duty Industrial Specification Grade

General

Color	Brown
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Specialty Receptacle
UPC	781786626287

Dimensions

Dimensions	3.28 in x 1.38 in x 0.86 in
Display Size	Standard Sized Product
Height	0.86 in
Length	3.28 in
Weight	0.35 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	277 V
Voltage Rating Description	277 V
Wattage	4155

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	7-15R
-------------	-------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - Bryant A-11 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-5782-SPEC-EN | REV 5/2023