



# Straight Blade Devices, Male Plug, Valise Series, Commercial Grade, Straight, 2-Pole 3-Wire Grounding, Insulation Displacement, 15A 125V, 5-15P

By Bryant  
Catalog # 5966VBK



Straight Blade Devices, Male Plug, Valise Series, Commercial Grade, Straight, 2-Pole 3-Wire Grounding, Insulation Displacement, 15A 125V, 5-15P, Black, Single Pack

## General

Application	Heavy Duty
Catalog Number	5966VBK
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Heavy Duty
Type	Plug
UPC	781786731769

## Dimensions

Dimensions	1.88 in x 1.25 in x 1.13 in
Display Size	Standard Sized
Height	1.13 in
Length	1.88 in
Weight	0.1 lb
Width	1.25 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Insulation Displacement
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire

## Certifications And Compliance

Nema Rating	5-15P
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY A-21 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - COBRA® Plugs and Connectors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-5966VBK-SPEC-EN | REV 6/2024