



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 60A 600V AC, Front Wired, Black

By Bryant
Catalog # 60002FWD



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 60A 600V AC, Front Wired, Black

General

Catalog Number	60002FWD
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Front Wire
UPC	781786631717

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	36000

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY E-12 Catalog Page](#)
- [Catalog Page - BRY G-2 Catalog Page](#)
- [Catalog Page - BRY G-6 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Motor Controllers and Disconnects](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-60002FWD-SPEC-EN | REV 6/2024