



# Locking Devices, Industrial, Flanged Receptacle, 20A 125V, 2- Pole 3-Wire Grounding, L5-20R, Screw Terminal, White

By Bryant  
Catalog # [70520ER](#)



Locking Devices, Industrial, Flanged Receptacle, 20A 125V, 2-  
Pole 3-Wire Grounding, L5-20R, Screw Terminal, White

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial Specification Grade

## General

|                              |  |
|------------------------------|--|
| Color                        | White  |
| Environmental Conditions     | Indoor Dry Unless Protected<br>By Additional Means |
| Item Type                    | 20A Flanged Receptacle                             |
| Material                     | Composite  |
| Material - Mounting Hardware | Screw Mounting                                     |
| Number Of Poles              | 2-Pole   |
| OEM Brand Name               | Hubbell Bryant                                     |
| Style                        | Equipment Base                                     |
| Type                         | Flanged Receptacle                                 |
| UPC                          | 781786688506                                       |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 2.88 in x 2.88 in x 2.02 in |
| Display Size | Standard Sized Product      |
| Height       | 2.02 in                     |
| Length       | 2.88 in                     |
| Width        | 2.88 in                     |

## Electrical Ratings

|                            |                 |
|----------------------------|-----------------|
| Amperage Rating            | 20 A            |
| Connectivity               | Terminal Screws |
| Current Rating             | 20 A            |
| Phase                      | Single Phase    |
| Voltage Rating             | 125 V           |
| Voltage Rating Description | 125V            |

## Conductor Related

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 3-Wire            |
| Wire Size       | #14 AWG to #8 AWG |

## Certifications and Compliance

|             |        |
|-------------|--------|
| Nema Rating | L5-20R |
|-------------|--------|

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog Page - Bryant H-8 Catalog page](#)  
[Catalog Page - Bryant Q-19 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-70520ER-SPEC-EN | REV 5/2023