



# Locking Devices, Marine Grade, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Yellow, Corrosion Resistant

By Bryant  
Catalog # 70520NCCR

Locking Devices, Marine Grade, Female Nylon Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Yellow/White, Corrosion Resistant

## Features

- Nickel-plated copper-alloy metallic components
- Molded of impact/chemical resistant high-visibility yellow nylon
- Stainless steel screws
- Receptacles have a one-piece grounding system with built-in self-grounding strap
- Triple Gripper® cord grip on plugs and connectors which feature three captive assembly screws to automatically tighten cord grip
- Individual wire pockets with clamp-type terminals

## Application

Heavy Duty Industrial

## General

Catalog Number	70520NCCR
Color	Yellow, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body



UPC 781786688605

## Dimensions

Display Size	Standard Sized Product
Height	3.9 in
Length	2.13 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L5-20R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY H-8 Catalog Page](#)
- [Catalog Page - BRY J-3 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 70520NCCR](#)

