



# Locking Devices, Isolated Ground, Industrial, Flush Receptacle, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Black

By Bryant  
Catalog # 70530IG



Locking Devices, Isolated Ground, Industrial, Flush Receptacle, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Orange.

## Features

- Limits electrical noise on the equipment grounding circuit by providing two grounding paths for the installation
- Nylon deep face design
- Triple-wipe brass line contacts
- Ground contacts and ground termination
- Nickel and brass plated wrap-around steel yoke

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	70530IG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Locking
Style	Isolated Ground
Type	Single Receptacle
UPC	781786688759

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product

Height	1.24 in
Length	3.28 in
Width	1.7 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L5-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY D-7 Catalog Page](#)  
[Catalog Page - BRY H-11 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 70530IG](#)