



# Locking Devices, Isolated Ground Industrial, Duplex Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Orange

By Bryant

Catalog # 70615DRIG



Locking Devices, Isolated Ground Industrial, Duplex Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Orange

## Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	70615DRIG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Duplex Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Locking
Style	Isolated Ground
Type	Duplex Receptacle
UPC	781786616318

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.17 in
Display Size	Standard Sized Product
Height	1.17 in

Length	3.28 in
Width	1.7 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L6-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY D-7 Catalog Page](#)  
[Catalog Page - BRY H-7 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 70615DRIG](#)