



Locking Devices, Industrial, Flanged Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, White

By Bryant
Catalog # 70615ER



Locking Devices, Industrial, Flanged Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, White

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	70615ER
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786703957

Dimensions

Dimensions	1.84 in x 2.50 in x 1.68 in
Display Size	Standard Sized Product
Height	1.68 in
Length	1.84 in
Width	2.5 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L6-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY Q-19 Catalog Page](#)
- [Catalog Page - BRY H-6 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-70615ER-SPEC-EN | REV 6/2024