



# Locking Devices, Industrial, Flush Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Black

By Bryant  
Catalog # [70615FR](#)

Locking Devices, Industrial, Flush Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Black



## Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786703551

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.17 in
Display Size	Standard Sized Product
Height	1.17 in
Length	3.28 in
Width	1.70 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L6-15R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-7 Catalog page](#)  
[Catalog Page - Bryant Q-18 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-70615FR-SPEC-EN | REV 5/2023