



Locking Devices, Industrial, Male Plug, 15A 250V, 2-Pole 3-Wire Grounding, L6-15P, Screw Terminal, Black and White

By Bryant
Catalog # [70615NP](#)



Locking Devices, Industrial, Male Plug, 15A 250V, 2-Pole 3-Wire Grounding, L6-15P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

General

Item Type	15A Triple Gripper Nylon Plug
Number Of Poles	2-Pole
Style	Internal Cord Clamp
Type	Plugs
UPC	781786666054

Dimensions

Dimensions	1.53 in x 1.53 in x 2.18 in
Height	2.18 in
Length	1.53 in
Width	1.53 in

Electrical Ratings

Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Nema Rating	L6-15P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-6 Catalog page](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-70615NP-SPEC-EN | REV 4/2023