



# Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 3-Wire Grounding, L6-30R, Screw Terminal, Black and White

By Bryant  
Catalog # 70630NCCR



Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 3-Wire Grounding, L6-30R, Screw Terminal, Black and White

## Features

- Nickel-plated copper-alloy metallic components
- Molded of impact/chemical resistant high-visibility yellow nylon
- Stainless steel screws
- Triple Gripper® cord grip on plugs and connectors which feature three captive assembly screws to automatically tighten cord grip
- Individual wire pockets with clamp-type terminals

## General

Application	Extra Heavy Duty Industrial
Catalog Number	70630NCCR
Color	Yellow, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Connector Body
UPC	781786706354

## Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized
Height	3.9 in
Length	2.13 in
Width	2.13 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L6-30R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY H-11 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-70630NCCR-SPEC-EN | REV 6/2024