



# Locking Devices, Industrial, Flanged Inlet, 30A 480V AC, 2-Pole 3-Wire Grounding, L8-30P, Screw Terminal, Black and White

By Bryant  
Catalog # [70830MB](#)



Locking Devices, Industrial, Flanged Inlet, 30A 480V AC, 2-Pole 3-Wire Grounding, L8-30P, Screw Terminal, White.

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Flanged Inlet
UPC	781786691162

## Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Dielectric Strength	Withstands 3500V
Voltage Rating	480 VAC
Voltage Rating Description	480V AC

## Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L8-30P
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-11 Catalog page](#)  
[Catalog Page - Bryant Q-19 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[WPC2 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, For Large Flanged Devices, Standard Size, Reinforced thermoplastic polyester](#)  
[70830NC - Locking Devices, Industrial, Female Connector Body, 30A 480V AC, 2-Pole 3-Wire Grounding, L8-30R, Screw Terminal, Black and White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-70830MB-SPEC-EN | REV 5/2023