



# Locking Devices, Industrial, Flanged Receptacle, 30A 600V AC, 2-Pole 3-Wire Grounding, L9- 30R, Screw Terminal, White

By Bryant  
Catalog # 70930ER



Locking Devices, Industrial, Flanged Receptacle, 30A 600V  
AC, 2-Pole 3-Wire Grounding, L9-30R, Screw Terminal, White

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786691902

## Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	600 VAC
Voltage Rating Description	600V AC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L9-30R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-11 Catalog page](#)  
[Catalog Page - Bryant Q-19 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[70930NP - Locking Devices, Industrial, Male Plug, 30A 600V  
AC, 2-Pole 3-Wire Grounding, L9-30P, Screw Terminal, Black  
and White](#)  
[WPC2 - Wallplates and Boxes, Weatherproof Covers, 1-Gang,  
For Large Flanged Devices, Standard Size, Reinforced  
thermoplastic polyester](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-70930ER-SPEC-EN | REV 5/2023