



Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray

By Bryant
Catalog # 7101

Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Black



Application

Heavy Duty Industrial

General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Two-Piece Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786627444

Dimensions

Display Size	Standard Sized Product
Height	2.78 in
Length	1.53 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Conductor Range	#14 AWG
Number Of Conductors	2-Pole Non-Grounding
Number Of Wires	2-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L2-20R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[P7BK - Wallplate, 1-Gang, 1.40" Opening, Black](#)
[8809ER - Locking Devices, Flanged Receptacle, 20A 250V, 2-Pole 2-Wire Non-Grounding, Non-NEMA, Black](#)
[7210B - Locking Devices, Industrial, Flush Receptacle, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray](#)
[SS7 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.40" Opening, Standard Size, Stainless Steel](#)
[RW57300 - Wallplates and Boxes, Weatherproof Hood, 1-Gang, Multi Opening, Vertical, Gray](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7101-SPEC-EN | REV 5/2023