



Locking Devices, Industrial, Flanged Receptacle, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, L10-20R, Screw Terminal, White

By Bryant
Catalog # 71020ER



Locking Devices, Industrial, Flanged Receptacle, 20A 125/250V AC, 3-Pole 3-Wire Grounding, L10-20R, Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	71020ER
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786692404

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in

Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L10-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY Q-19 Catalog Page](#)
[Catalog Page - BRY H-9 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71020ER](#)