



Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray

By Bryant
Catalog # 7102N



Locking Devices, Industrial, Plug, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20, Screw Terminal, Black/White Nylon Polarized, with Non-metallic Cord Grip

Features

- Plug
- 20A 250V
- 2-Pole 2-Wire Non-Grounding
- L2-20
- Screw Terminal

Application

Heavy Duty Industrial

General

Catalog Number	7102N
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Two-Piece Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plugs
UPC	781786715509

Dimensions

Dimensions	1.53 in x 1.53 in x 1.97 in
Display Size	Standard Sized Product
Height	1.97 in
Length	1.53 in
Width	1.53 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Conductor Range	#14 AWG
Number Of Wires	2-Wire
Number of Conductors	2-Pole Non-Grounding

Certifications And Compliance

Nema Rating	L2-20P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-5 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7102N](#)