



## Locking Devices, Industrial, Flanged Inlet, 30A 125/250V, 3-Pole 3-Wire Non Grounding, L10-30P, Screw Terminal, White

By Bryant  
Catalog # [71030MB](#)



Locking Devices, Industrial, Flanged Inlet, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, L10-30P, Screw Terminal, White.

### Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

### Application

Extra Heavy Duty Industrial

### General

Catalog Number	71030MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786692664

### Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

### Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Dielectric Strength	Withstands 3500V
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

### Certifications And Compliance

Nema Rating	L10-30P
-------------	---------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - BRY Q-19 Catalog Page](#)  
[Catalog Page - BRY H-12 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 71030MB](#)