



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-3OR, Screw Terminal, White

By Bryant
Catalog # [71230ER](#)



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase
Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-3OR, Screw
Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786694309

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L12-3OR
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-12 Catalog page](#)
[Catalog Page - Bryant Q-19 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[WPC2 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, For Large Flanged Devices, Standard Size, Reinforced thermoplastic polyester](#)
[71230NP - Locking Devices, Industrial, Male Plug, 30A 3- Phase Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-3OP, Screw Terminal, Black and White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-71230ER-SPEC-EN | REV 5/2023