



# Locking Devices, Industrial, Flanged Inlet, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30P, Screw Terminal, White, With Weatherproof Cover



By Bryant  
Catalog # 71430MBWP

Locking Devices, Industrial, Flanged Inlet, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30P, Screw Terminal, White, With Weatherproof Cover

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included
- Weather Protective Cover

## Application

- Extra Heavy Duty Industrial

## General

Catalog Number	71430MBWP
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Weather Resistant
Insulation	Insulated Body
Item Type	30A Weather Protective Power Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Weatherprotective
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786695375

## Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Dielectric Strength	Withstands 3500V
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L14-30P
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY H-12 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)