



Locking Devices, Industrial, Female Connector Body, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30R, Screw Terminal, Black and White

By Bryant
Catalog # 71430NC



Locking Devices, Industrial, Female Connector Body, 30A 125/250V AC, 3-Pole 4-Wire Grounding, L14-30R, Screw Terminal, Black and White.

General

Application	Heavy Duty Industrial
Catalog Number	71430NC
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786695399

Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product
Height	3.9 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L14-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	2250

Product Assets

- [Catalog Page - BRY H-12 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Literature - General Literature - Pool Pump Receptacle Kit](#)
- [Literature - General Literature - Healthcare Solutions](#)
- [Literature - General Literature - BRYANT® Wiring Devices](#)
- [Literature - General Literature - Power Disruption Solutions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-71430NC-SPEC-EN | REV 6/2024