



# Locking Devices, Industrial, Flanged Inlet, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-30P, Screw Terminal, White

By Bryant  
Catalog # 71530MB



Locking Devices, Industrial, Flanged Inlet, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-30P, Screw Terminal, White

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial

## General

Catalog Number	71530MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786696167

## Dimensions

Dimensions 2.88 in x 2.88 in x 2.02 in

Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Dielectric Strength	Withstands 3500V
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250V AC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L15-30P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY Q-19 Catalog Page](#)  
[Catalog Page - BRY H-12 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 71530MB](#)