

# Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-20P, Screw Terminal, Black and White

By Bryant  
Catalog # 71620NP



Locking Devices, Industrial, Male Nylon Plug, 20A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-20P, Screw Terminal, Black and White

## Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

## Application

Extra Heavy Duty Industrial

## General

Catalog Number	71620NP
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786696921

## Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized

Height	2.86 in
Length	2.13 in
Width	2.13 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L16-20P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	2250

## Product Assets

[Catalog Page - BRY H-9 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 71620NP](#)