



Locking Devices, Industrial, Male Plug, 20A 3- Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, L18-20P, Screw Terminal, Black and White

By Bryant
Catalog # 71820NP



Locking Devices, Industrial, Male Nylon Plug, 20A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, L18-20P, Screw Terminal, Black and White.

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

General

Application	Extra Heavy Duty Industrial
Catalog Number	71820NP
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786698222

Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L18-20P
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-10 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-71820NP-SPEC-EN | REV 6/2024