



Locking Devices, Industrial, Female Connector Body, 20A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20R, Screw Terminal, Black and White

By Bryant
Catalog # 71920NC



Locking Devices, Industrial, Female Nylon Connector Body, 20A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20R, Screw Terminal, Black and White.

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Heavy Duty Industrial

General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786698994

Dimensions

Display Size	Standard Sized Product
Height	3.90 in
Length	2.13 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480 VAC

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Conductors	4-Wire Non-Grounding
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L19-20R
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [SS720 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.60" Opening, Standard Size, Stainless Steel](#)
- [71920NP - Locking Devices, Industrial, Male Plug, 20A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20P, Screw Terminal, Black and White](#)
- [72002BC - Locking Devices, Accessories, Long Weatherproofing Boot, For 20A and 30A, Yellow](#)
- [72002BCB - Locking Devices, Accessories, Long Weatherproofing Boot, For 20A and 30A, Black](#)
- [NP720GY - Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1\) 1.60" Opening, Gray](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-71920NC-SPEC-EN | REV 5/2023