



# Locking Devices, Industrial, Male Plug, 20A 3- PhaseWye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20P, Screw Terminal, Black and White

By Bryant  
Catalog # [71920NP](#)



Locking Devices, Industrial, Male Nylon Plug, 20A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20P, Screw Terminal, Black and White.

## Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

## Application

Extra Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786699021

## Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480 VAC

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L19-20P
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-10 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[NP720GY - Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1\) 1.60" Opening, Gray](#)  
[7420B - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 1.62" Opening, Standard Size, Cast Aluminum](#)  
[NP720BK - Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1\) 1.60" Opening, Black](#)  
[71920NC - Locking Devices, Industrial, Female Connector Body, 20A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20R, Screw Terminal, Black and White](#)  
[71920MB - Locking Devices, Industrial, Flanged Inlet, 20A 3-PhaseWye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-20P, Screw Terminal, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-71920NP-SPEC-EN | REV 5/2023