



# Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-30R, Screw Terminal, Black

By Bryant  
Catalog # [71930FR](#)



Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-30R, Screw Terminal, Black

## Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786699434

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.70 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480V AC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L19-20R
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant Q-18 Catalog page](#)  
[Catalog Page - Bryant H-13 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[7420B - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 1.62" Opening, Standard Size, Cast Aluminum](#)  
[20405 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, For 30A Power Interrupting, Standard Size, Cast Aluminum, New Style](#)  
[71930NP - Locking Devices, Industrial, Male Plug, 30A 3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non-Grounding, L19-30P, Screw Terminal, Black and White](#)  
[SB720 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.60" Opening, Standard Size, Brass](#)  
[SS720 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.60" Opening, Standard Size, Stainless Steel](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-71930FR-SPEC-EN | REV 5/2023