



# Locking Devices, Industrial, Flanged Receptacle, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20R, Screw Terminal, White

By Bryant  
Catalog # 72020ER



Locking Devices, Industrial, Flanged Receptacle, 20A 3-Phase Wye 347/600V AC, 4-Pole 4-Wire Grounding, L20-20R, Screw Terminal, White

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	72020ER
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786700208

## Dimensions

Dimensions	3.06 in x 3.06 in x 2.03 in
Display Size	Standard Sized Product

Height	2.03 in
Length	3.06 in
Width	3.06 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480V AC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L20-20R
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY H-10 Catalog Page](#)  
[Catalog Page - BRY Q-19 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 72020ER](#)