



## Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20R, Screw Terminal, Black

By Bryant  
Catalog # [72020FR](#)



Locking Devices, Industrial, Flush Nylon Receptacle, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20R, Screw Terminal, Black

### Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

### Application

Extra Heavy Duty Industrial Specification Grade

### General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786700239

### Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.70 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480V AC

### Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

### Certifications and Compliance

Nema Rating	L20-20R
-------------	---------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant H-10 Catalog page](#)  
[Catalog Page - Bryant Q-18 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

### Related Products

[SS720 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.60" Opening, Standard Size, Stainless Steel](#)  
[72020MB - Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20P, Screw Terminal, White](#)  
[NP720W - Wallplates and Box Covers, Wallplate, Nylon, 1- Gang, 1\) 1.60" Opening, White](#)  
[72020NP - Locking Devices, Industrial, Male Plug, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20P, Screw Terminal, Black and White](#)  
[72020NC - Locking Devices, Industrial, Female Connector Body, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20R, Screw Terminal, Black and White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-72020FR-SPEC-EN | REV 5/2023