



# Locking Devices, Industrial, Female Connector Body, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20R, Screw Terminal, Black and White

By Bryant  
Catalog # [72020NC](#)



Locking Devices, Industrial, Female Nylon Connector Body, 20A 3-Phase Wye 347/600V AC, 4-Pole 4-Wire Non-Grounding, L20-20R, Screw Terminal, Black and White.

## Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

## Application

Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786700291

## Dimensions

Display Size	Standard Sized Product
Height	3.90 in
Length	2.13 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	3 Phase Y 347/600 VAC
Voltage Rating Description	3 Phase Y 347/600 VAC

## Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Conductors	4-Wire Non-Grounding
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L20-20R
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-10 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[72020NP - Locking Devices, Industrial, Male Plug, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20P, Screw Terminal, Black and White](#)  
[NP720BK - Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1\) 1.60" Opening, Black](#)  
[SB720 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.60" Opening, Standard Size, Brass](#)  
[NP720 - Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1\) 1.60" Opening, Brown](#)  
[72020MB - Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20P, Screw Terminal, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-72020NC-SPEC-EN | REV 5/2023