



# Locking Devices, Industrial, Male Plug, 20A 3- Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20P, Screw Terminal, Black and White

By Bryant  
Catalog # 72020NP



Locking Devices, Industrial, Male Nylon Plug, 20A 3-Phase Wye 347/600V AC, 4-Pole 4-Wire Non-Grounding, L20-20P, Screw Terminal, Black and White.

## Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

## Application

Extra Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786700321

## Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase Y 347/600 VAC
Voltage Rating Description	3 Phase Y 347/600 VAC

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L20-20P
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-10 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [NP720GY - Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1\) 1.60" Opening, Gray](#)
- [NP720I - Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1\) 1.60" Opening, Ivory](#)
- [NP720W - Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1\) 1.60" Opening, White](#)
- [72020FR - Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20R, Screw Terminal, Black](#)
- [72002BC - Locking Devices, Accessories, Long Weatherproofing Boot, For 20A and 30A, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-72020NP-SPEC-EN | REV 5/2023