



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-30R, Screw Terminal, White

By Bryant
Catalog # 72030ER



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-30R, Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	72030ER
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786700505

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase Y 347/600 VAC
Voltage Rating Description	3 Phase Y 347/600V AC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L20-20R
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY Q-19 Catalog Page](#)
- [Catalog Page - BRY H-13 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-72030ER-SPEC-EN | REV 6/2024