



Locking Devices, Industrial, Flush Receptacle, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray

By Bryant
Catalog # 7210B

Locking Devices, Industrial, Flush Receptacle, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Black



Application

Extra Heavy Duty Industrial Specification Grade

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786627765

Dimensions

Display Size	Standard Sized Product
Height	1.00 in
Length	3.28 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

Conductor Related

Number Of Wires	2-Wire
Wire Size	#14 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L2-20R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7102N - Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray](#)

[RW51550 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, 1.40" Opening, Vertical, Gray](#)

[8808MB - Locking Devices, Flanged Inlet, 20A 250V, 2-Pole 2-Wire Non-Grounding, Non-NEMA, Black](#)

[7101 - Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray](#)

[8809ER - Locking Devices, Flanged Receptacle, 20A 250V, 2-Pole 2-Wire Non-Grounding, Non-NEMA, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7210B-SPEC-EN | REV 5/2023