



# Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-30R, Screw Terminal, White

By Bryant  
Catalog # 72130ER



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-30R, Screw Terminal, White

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial Specification Grade

## General

|                              |   |
|------------------------------|---|
| Catalog Number               | 72130ER   |
| Color                        | White   |
| EU RoHS Indicator            | Yes   |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means |
| Item Type                    | 30A Flanged Receptacle                          |
| Material                     | Composite                                       |
| Material - Mounting Hardware | Screw Mounting                                  |
| Number Of Poles              | 4-Pole  |
| OEM Brand Name               | Hubbell Bryant                                  |
| Style                        | Equipment Base                                  |
| Type                         | Flanged Receptacle                              |
| UPC                          | 781786701403                                    |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 2.88 in x 2.88 in x 2.02 in |
| Display Size | Standard Sized Product      |

|        |         |
|--------|---------|
| Height | 2.02 in |
| Length | 2.88 in |
| Width  | 2.88 in |

## Electrical Ratings

|                            |                       |
|----------------------------|-----------------------|
| Amperage Rating            | 30 A                  |
| Connectivity               | Terminal Screws       |
| Current Rating             | 30 A                  |
| Phase                      | Three Phase           |
| Voltage Rating             | 3 Phase Y 120/208 VAC |
| Voltage Rating Description | 3 Phase Y 120/208V AC |

## Conductor Related

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 5-Wire            |
| Wire Size       | #14 AWG to #8 AWG |

## Certifications And Compliance

|             |         |
|-------------|---------|
| Nema Rating | L21-30R |
|-------------|---------|

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog Page - BRY Q-19 Catalog Page](#)  
[Catalog Page - BRY H-13 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 72130ER](#)