



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30R, Screw Terminal, White

By Bryant
Catalog # 72230ER



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30R, Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	72230ER
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786702103

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product

Height	2.02 in
Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480V AC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L22-30R
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY Q-19 Catalog Page](#)
[Catalog Page - BRY H-13 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 72230ER](#)