



## Locking Devices, Industrial, Male Plug, 30A 3- Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30P, Screw Terminal, Black and White

By Bryant  
Catalog # 72230NP



Locking Devices, Industrial, Male Plug, 30A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-30P, Screw Terminal, Black and White.

### Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

### Application

Extra Heavy Duty Industrial

### General

Catalog Number	72230NP
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786702226

### Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

### Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480 VAC

### Conductor Related

Cord Type	All Listed Portables
Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG

### Certifications And Compliance

Nema Rating	L22-30P
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	10
Pallet Quantity	2340

### Product Assets

[Catalog Page - BRY H-13 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand