



Locking Devices, Industrial, Flush Receptacle, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7310



Locking Devices, Industrial, Flush Receptacle, 20A 125/250V AC, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

Features

- Flush Receptacle
- 20A 125/250V AC
- 3-Pole 3-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	7310
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Receptacle-For Replacement Use
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786628007

Dimensions

Dimensions	3.28 in x 1.71 in x 1.14 in
Display Size	Standard Sized Product

Height	1.14 in
Length	3.28 in
Width	1.71 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Multi Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY Q-18 Catalog Page](#)
[Catalog Page - BRY H-16 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7310](#)