



Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [7314NB](#)



Locking Devices, Industrial, Female Nylon Connector Body, 20A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

Application

Heavy Duty Industrial

General

Color	Sentinel Yellow
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Nylon Connector-For Replacement Use
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786616370

Dimensions

Display Size	Standard Sized Product
Height	3.73 in
Length	2.11 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Conductors	3-Wire Non-Grounding
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-16 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7314NB-SPEC-EN | REV 7/2023