



Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7410



Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

Application

Extra Heavy Duty Industrial Specification Grade

General

| | |
|------------------------------|---|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | 20A Single Receptacle-For Replacement Use |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 4-Pole |
| OEM Brand Name | Hubbell Bryant |
| Style | Single Receptacle |
| Type | Receptacle |
| UPC | 781786628311 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.71 in x 1.14 in |
| Display Size | Standard Sized Product |
| Height | 1.14 in |
| Length | 3.28 in |
| Width | 1.71 in |

Electrical Ratings

| | |
|----------------------------|-----------------------|
| Amperage Rating | 20 A |
| Connectivity | Terminal Screws |
| Current Rating | 20 A |
| Phase | Three Phase |
| Voltage Rating | 3 Phase Y 120/208 VAC |
| Voltage Rating Description | 3 Phase Y 120/208V AC |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 4-Wire |
| Wire Size | #14 AWG to #8 AWG |

Certifications and Compliance

| | |
|-------------|----------|
| Nema Rating | Non-NEMA |
|-------------|----------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Bryant Q-18 Catalog page](#)
[Catalog Page - Bryant H-16 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7410-SPEC-EN | REV 7/2023