



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black & White

By Bryant
Catalog # [7464N](#)



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black & White

Features

Abuse resistant nylon housing

Application

Heavy Duty Industrial

General

EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Female Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Non-Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plugs
UPC	781786638501

Dimensions

Dimensions	1.25 in x 1.25 in x 2.15 in
Display Size	Midget NEMA Locking
Height	2.15 in
Length	1.25 in
Width	1.25 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG
Number Of Wires	2-Wire
Number of Conductors	2-Pole Non-Grounding
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Nema Rating	ML-1R
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	16500

Product Assets

[Catalog Page - BRY H-4 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-7464N-SPEC-EN | REV 5/2024