



# Locking Devices, Industrial, Male Plug, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15P, Screw Terminal, Black

By Bryant  
Catalog # 7548

Locking Devices, Industrial, Male Plug, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15P, Screw Terminal, Black



## Application

Extra Heavy Duty Industrial

## General

|                              |   |
|------------------------------|---|
| Color                        | Black   |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means |
| Item Type                    | 15A Nylon Plug                                  |
| Material                     | Composite                                       |
| Material - Mounting Hardware | Cord Mounted                                    |
| Number Of Poles              | 2-Pole  |
| OEM Brand Name               | Hubbell Bryant                                  |
| Style                        | Internal Cord Clamp                             |
| Type                         | Plugs   |
| UPC                          | 781786629257                                    |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 1.53 in x 1.53 in x 1.97 in |
| Display Size | Standard Sized              |
| Height       | 1.97 in                     |
| Length       | 1.53 in                     |
| Width        | 1.53 in                     |

## Electrical Ratings

|                            |                 |
|----------------------------|-----------------|
| Amperage Rating            | 15 A            |
| Connectivity               | Screw Terminals |
| Current Rating             | 15 A            |
| Phase                      | Single Phase    |
| Voltage Rating             | 125 V           |
| Voltage Rating Description | 125 V           |

## Conductor Related

|                 |                      |
|-----------------|----------------------|
| Cord Type       | All Listed Portables |
| Number Of Wires | 2-Wire               |
| Wire Size       | #14 AWG to #10 AWG   |

## Certifications and Compliance

|             |        |
|-------------|--------|
| Nema Rating | L1-15P |
|-------------|--------|

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

## Product Assets

[Catalog Page - Bryant H-5 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [RW51550 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, 1.40" Opening, Vertical, Gray](#)
- [7526 - Locking Devices, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15P, Screw Terminal, White](#)
- [7535 - Locking Devices, Industrial, Receptacle, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15R, Screw Terminal, Black](#)
- [7523 - Locking Devices, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15P, Screw Terminal, White](#)
- [P7BK - Wallplate, 1-Gang, 1.40" Opening, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-7548-SPEC-EN | REV 7/2023