



Locking Devices, Marine Grade, Female Connector Body, 15A 125V/10A 250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, Yellow

By Bryant
Catalog # [7565NCCR](#)



Locking Devices, Marine Grade, Female Connector Body, 10A 250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, Corrosion-Resistant, Yellow

Features

- Female Connector Body
- 10A 250V
- 3-Pole 3-Wire Non Grounding
- Non-NEMA
- Screw Terminal

Application

Heavy Duty Industrial

General

Catalog Number	7565NCCR
Color	Black, White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	10A Triple Gripper Nylon Connector Non-NEMA
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786010604

Dimensions

Dimensions	1.53 in x 1.53 in x 2.95 in
Display Size	Standard Sized Product
Height	2.95 in
Length	1.53 in
Width	1.53 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Non-Grounding
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-15 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7565NCCR](#)